




ITEM	MOLEX P/N	OUTER TUBE (AFTER SHRINKAGE)	
		OD	LENGTH
1.	1069200000	2.3±0.1	40±0.1
2.	1069200001	2.4±0.1	45±0.1
3.	1069200002	2.6±0.1	60±0.1



NOTE:
1. THE PACKAGE METHOD PER MOLEX STANDARD.

DOCUMENT STATUS	P1	RELEASE DATE	2022/11/27	23:55:00
-----------------	----	--------------	------------	----------

FUNCTIONAL SYMBOLS $\frac{F}{E} = 0$ $\frac{F}{E} = 0$ $\frac{F}{P} = 0$ DIVISIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
	DIMENSION UNITS		SCALE		CURRENT REV DESC: RESTRICTED TYPE GENERAL MARKET WAS MOLEX INTERNAL EC NO: 729937 DRWN: PAWANC 2022/11/25 CHK'D: NCHE08 2022/11/27 APPR: NCHE08 2022/11/27				molex				
	mm		1:1										
	GENERAL TOLERANCES (UNLESS SPECIFIED)								HST 1C				
	ANGULAR TOL ± 0.5°												
	4 PLACES		±		INITIAL REVISION: DRWN: PAWANC 2022/10/03 APPR: NCHE08 2022/10/13				DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
	3 PLACES		±						1069200000		PSD	000	A1
	2 PLACES		±										
	1 PLACE		±						MATERIAL NUMBER		CUSTOMER		SHEET NUMBER
	0 PLACES		±						106920		GENERAL MARKET		1 OF 1
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES					
						B-SIZE		106920					