



SIX ROW – RIGHT ANGLE PTH RCPT STRAIGHT PTH RCPT

RM6 – RECOMMENDED BOARD LAYOUT


0.075" | 162 THROUGH 402 CONTACTS



DIMENSIONS		
SIZE	A	B
162	2.400	2.000
204	2.925	2.525
252	3.525	3.125
300	4.125	3.725
360	4.875	4.475
402	5.400	5.000



RIGHT ANGLE PTH RECEPTACLE
PC BOARD VIEWED FROM COMPONENT SIDE



STRAIGHT PTH RECEPTACLE
PC BOARD VIEWED FROM COMPONENT SIDE

*COMPLIANT TERMINATION REQUIREMENTS:
Board Material: FR-4 w/ 1.0 oz. copper
Minimum nominal board thickness: .062"
Drilled hole: .0319"-.0339"
Copper plating thickness: .0010" minimum
Tin-lead plating thickness: .0006" maximum
Electroplated tin-lead composition: 63/37 (Sn/Pb)
Finished hole diameter: .028"±.002"

SIZE	CONTACT ID		SIZE	CONTACT ID	
162	84	87 90	300	153	158 159
	83	86 89		152	155 158
	82	85 88		151	154 157
204	109	108 111	360	183	188 189
	104	107 110		182	185 188
	103	106 109		181	184 187
252	129	132 135	402	204	207 210
	124	127 130		203	206 209
	123	126 129		202	205 208