



## 2 • ROW


Straight PTH Rcpt

.050"


**WB**

20 thru 132 Contacts

Recommended  
Board Layout



| DIMENSIONS |       |       |
|------------|-------|-------|
| SIZE       | A     | B     |
| 20         | .750  | .450  |
| 30         | 1.000 | .700  |
| 40         | 1.250 | .950  |
| 50         | 1.500 | 1.200 |
| 60         | 1.750 | 1.450 |
| 70         | 2.000 | 1.700 |
| 80         | 2.250 | 1.950 |
| 90         | 2.500 | 2.200 |
| 100        | 2.750 | 2.450 |
| 110        | 3.000 | 2.700 |
| 128        | 3.450 | 3.150 |
| 132        | 3.550 | 3.250 |



STRAIGHT PTH RECEPTACLE  
PC BOARD VIEWED FROM COMPONENT SIDE

| SIZE | CONTACT ID | SIZE | CONTACT ID | SIZE | CONTACT ID |
|------|------------|------|------------|------|------------|
| 20   |            | 60   |            | 100  |            |
| 30   |            | 70   |            | 110  |            |
| 40   |            | 80   |            | 128  |            |
| 50   |            | 90   |            | 132  |            |