


2 • ROW Straight SMT Plug

.050"

WBB, WBA

20 thru 132 Contacts

Recommended
Board Layout



DIMENSIONS		
SIZE	A	B
20	.900	.450
30	1.150	.700
40	1.400	.950
50	1.650	1.200
60	1.900	1.450
70	2.150	1.700
80	2.400	1.950
90	2.650	2.200
100	2.900	2.450
110	3.150	2.700
128	3.600	3.150
132	3.700	3.250

STRAIGHT SMT PLUG

SIZE	CONTACT ID	SIZE	CONTACT ID	SIZE	CONTACT ID
20	C10 > C20 C9 > C19 C8 > C18 C7 > C17 C6 > C16 C5 > C15 C4 > C14 C3 > C13 C2 > C12 C1 > C11	60	C30 > C60 C29 > C59 C28 > C58 C3 > C33 C2 > C32 C1 > C31	100	C50 > C100 C49 > C99 C48 > C98 C3 > C53 C2 > C52 C1 > C51
30	C15 > C30 C14 > C29 C13 > C28 C3 > C18 C2 > C17 C1 > C16	70	C35 > C70 C34 > C69 C33 > C68 C3 > C38 C2 > C37 C1 > C36	110	C55 > C110 C54 > C109 C53 > C108 C3 > C58 C2 > C57 C1 > C56
40	C20 > C40 C19 > C39 C18 > C38 C3 > C23 C2 > C22 C1 > C21	80	C40 > C80 C39 > C79 C38 > C78 C3 > C43 C2 > C42 C1 > C41	128	C64 > C128 C63 > C127 C62 > C126 C3 > C67 C2 > C66 C1 > C65
50	C25 > C50 C24 > C49 C23 > C48 C3 > C28 C2 > C27 C1 > C26	90	C45 > C90 C44 > C89 C43 > C88 C3 > C48 C2 > C47 C1 > C46	132	C66 > C132 C65 > C131 C64 > C130 C3 > C69 C2 > C68 C1 > C67