




CABLE-TO-CABLE (JUMPER ASSEMBLY)

MM - RUGGED METAL &
MN - RUGGED PLASTIC
0.050" | 9 THROUGH 100 CONTACTS

MM-202-031-P51-22WA
(METAL)
MN-201-031-P51-22WA
(PLASTIC)



DIMENSIONS									
Size	Contact Row	A	B		C	D	E	H	Hardware
			Plug MAX	RCPT MAX			Potting Well MAX		
9	2	0.775	0.334	0.400	0.390	0.565	0.270	0.298	#2-56 UNC THD (0.092 DIA THROUGH)
15		0.925	0.484	0.550	0.540	0.715			
21		1.075	0.634	0.700	0.690	0.865			
25		1.175	0.734	0.800	0.790	0.965			
31		1.325	0.884	0.950	0.940	1.115			
37		1.475	1.034	1.100	1.090	1.265			
51**		1.825	1.384	1.450	1.440	1.615			
51	3	1.425	0.984	1.050	1.040	1.215	0.310	0.341	#2-56 UNC THD (0.092 DIA THROUGH)
69*		1.725	1.284	1.350	1.340	1.515			
100	4	2.160	1.384	1.508	1.432	1.800	0.360	0.384	#4-40 UNC THD (0.147 DIA THROUGH)

* 69 Position connectors are available in metal only.
** Two row, 51 position connectors are available in metal only, (non MIL-SPEC interface).