




CABLE-TO-CABLE (JUMPER ASSEMBLY)

MQ – LOW-PROFILE METAL &
MP – LOW-PROFILE PLASTIC
0.050" | 9 THROUGH 51 CONTACTS



MQ-2J2-031-PS1-22WA
(METAL)
MP-2J1-031-PS1-22WA
(PLASTIC)



DIMENSIONS									
Size	Contact Row	A	B		C	D	E	H	Hardware
			Plug MAX	RCPT MAX			Potting Well MAX		
9	2	0.778	0.292	0.378	0.398	0.565	0.173	0.208	#2-56 UNC THD (0.092 DIA THROUGH)
15		0.928	0.442	0.528	0.548	0.715			
21		1.078	0.592	0.678	0.698	0.865			
25		1.178	0.692	0.778	0.798	0.965			
31		1.328	0.842	0.928	0.948	1.115			
37		1.478	0.992	1.078	1.098	1.265			
51	3	1.428	0.942	1.028	1.048	1.215	0.220	0.250	