


RIGHT-ANGLE BOARDMOUNT LOW-PROFILE (NARROW FOOTPRINT)

MS & MR
0.050" | 9 THRU 51 CONTACTS

MATING MATRIX	
Connector	Mates With
MS-25...	MP, MO, MR, MS receptacles
MR-25...	MP, MO, MR, MS receptacles
MS-26..	MP, MO, MR, MS plugs
MR-26...	MP, MO, MR, MS plugs



DIMENSIONS																	
Size	Contact Row	A	B		C		D	F	H	J		W	X MAX	Y MAX	Z	Hardware	Mounting Hole
			Plug MAX	RCPT MAX	Plug MAX	RCPT MAX				Plug	RCPT						
9	2	0.778	0.292	0.378	0.134	0.218	0.565	0.020	0.208	0.199	0.180	0.250	0.420	0.420	0.775	#2-56 UNC THD	0.096 DIA or #2-56 UNC Threaded Insert
15		0.928	0.442	0.528			0.715	0.120							0.925		
21		1.078	0.592	0.678			0.865								1.075		
25		1.178	0.692	0.778			0.965								1.175		
31		1.328	0.842	0.928			1.115						0.450	0.520	1.080		
37		1.478	0.992	1.078			1.265	1.180									
51	3	1.428	0.942	1.028	0.177	0.260	1.215	0.150	0.250			0.300	0.425	0.650	1.220		