


RIGHT-ANGLE BOARDMOUNT LOW-PROFILE (BLIND-CLEARANCE CUT)



MS
0.050" | 9 THROUGH 51 CONTACTS

MATING MATRIX	
Connector	Mates With
MS-2L	MP, MO, MR, MS receptacles
MS-2V.	MP, MO, MR, MS plugs

MS-2T3-037-325-220S
(PLUG)



MS-2V3-037-435-220S
(RCPT)



DIMENSIONS																		
Size	Contact Row	A	B		C		D	F	H	J		K	W	X MAX	Y MAX	Z	Hardware	Mounting Hole
			Plug MAX	RCPT MAX	Plug MAX	RCPT MAX				Plug	RCPT							
9	2	0.778	0.292	0.378	0.134	0.218	0.565	0.020	0.208	0.199	0.180	0.067	0.250	0.420	0.420	0.775	#2-56 UNC THD	0.096 DIA or #2-56 UNC Threaded Insert
15		0.928	0.442	0.528			0.715	0.120										
21		1.078	0.592	0.678			0.865											
25		1.178	0.692	0.778			0.965											
31		1.328	0.842	0.928			1.115											
37		1.478	0.992	1.078			1.265											
51	3	1.428	0.942	1.028	0.177	0.260	1.215	0.150	0.250			0.087	0.300	0.425	0.650	1.220		