



CABLE-TO-BOARD (NARROW FOOTPRINT)

**MM & MN – RUGGED BOARD MOUNT &
MK & ML – RUGGED CABLE**
0.050" | 9 THROUGH 100 CONTACTS

MM-312-051-153-4400
(METAL)
MN-311-051-153-4400
(PLASTIC)



MK-322-051-235-2200
(METAL)
ML-321-051-235-2200
(PLASTIC)



DIMENSIONS

| Size | Contact Row | A | B | | C | D | E Potting Well Max | H | X | Z MAX | Hardware | Mounting Hole |
|------|-------------|-------|-------------|-------------|-------|-------|-----------------------|-------|-------|----------|---|---|
| | | | Plug MAX | RCPT MAX | | | | | | | | |
| 9 | 2 | 0.775 | 0.334 | 0.400 | 0.390 | 0.565 | 0.270 | 0.298 | 1.150 | 1.390 | #2-56 UNC THD (0.092 DIA Through) | 0.096 DIA or #2-56 UNC Threaded Insert |
| 15 | | 0.925 | 0.484 | 0.550 | 0.540 | 0.715 | | | | | | |
| 21 | | 1.075 | 0.634 | 0.700 | 0.690 | 0.865 | | | | | | |
| 25 | | 1.175 | 0.734 | 0.800 | 0.790 | 0.965 | | | | | | |
| 31 | | 1.325 | 0.884 | 0.950 | 0.940 | 1.115 | | | | | | |
| 37 | 1.475 | 1.034 | 1.100 | 1.090 | 1.265 | | | | | | | |
| 51 | 3 | 1.425 | 0.984 | 1.050 | 1.040 | 1.215 | 0.310 | 0.341 | 2.000 | 2.270 | #4-40 UNC THD (0.147 DIA Through) | 0.125 DIA or #2-56 UNC Threaded Insert |
| 100 | 4 | 2.160 | 1.384 | 1.508 | 1.432 | 1.800 | 0.360 | 0.384 | 2.800 | 3.240 | | |