


CABLE-TO-BOARD (NARROW FOOTPRINT)

MK & ML – RUGGED BOARD MOUNT &
MM & MN – RUGGED CABLE
0.050" | 9 THROUGH 100 CONTACTS



DIMENSIONS												
Size	Contact Row	A	B		C	D	E Potting Well Max	H	X	Z MAX	Hardware	Mounting Hole
			Plug MAX	RCPT MAX								
9	2	0.775	0.334	0.400	0.390	0.565	0.270	0.298	1.150	1.390	#2-56 UNC THD	0.096 DIA or #2-56 UNC Threaded Insert
15		0.925	0.484	0.550	0.540	0.715			1.450	1.690		
21		1.075	0.634	0.700	0.690	0.865			1.500	1.740		
25		1.175	0.734	0.800	0.790	0.965			1.800	2.040		
31		1.325	0.884	0.950	0.940	1.115			2.100	2.340		
37	3	1.475	1.034	1.100	1.090	1.265	0.310	0.341	2.000	2.270	#4-40 UNC THD	0.125 DIA or #2-56 UNC Threaded Insert
51		1.425	0.984	1.050	1.040	1.215			2.800	3.240		
100	4	2.160	1.384	1.508	1.432	1.800	0.360	0.384	2.800	3.240	#4-40 UNC THD	0.125 DIA or #2-56 UNC Threaded Insert