



# CABLE-TO-BOARD (STANDARD FOOTPRINT)

**MK & ML – RUGGED BOARD MOUNT &  
MM & MN – RUGGED CABLE**  
0.050" | 9 THROUGH 100 CONTACTS



## DIMENSIONS

Size	Contact Row	A	B		C	D	E Potting Well Max	H	P	X	Y	Z**	Hardware	
			Plug MAX	RCPT MAX										
9	2	0.775	0.334	0.400	0.390	0.565	0.270	0.298	0.210	0.298	0.280	0.390	#2-56 UNC THD (#2-56 Clearance or #2-56 UNC Threaded Insert)	
15		0.925	0.484	0.550	0.540	0.715								0.540
21		1.075	0.634	0.700	0.690	0.865								0.690
25		1.175	0.734	0.800	0.790	0.965								0.780
31		1.325	0.884	0.950	0.940	1.115								0.930
37		1.475	1.034	1.100	1.090	1.265								1.080
51	3	1.425	0.984	1.050	1.040	1.215	0.310	0.341	0.219	0.390	0.325	1.046	#4-40 UNC THD (#4-40 Clearance or #4-40 UNC Threaded Insert)	
69		1.725	1.284	1.350	1.340	1.515						1.346		
100	4	2.160	1.384	1.508	1.432	1.800	0.360	0.384	0.216	0.490	0.379	1.530	#4-40 UNC THD (#4-40 Clearance or #4-40 UNC Threaded Insert)	

\* 69 Position connectors are available in metal only.

\*\* "Z" Dimension for turning jackscrew only.