



BOARD SMT-TO-CABLE

MM - RUGGED METAL &
MN - RUGGED PLASTIC
0.050" | 9 THROUGH 51 CONTACTS

MM-212-025-175-3205
(METAL)
MN-211-025-175-3205
(PLASTIC)



MM-222-025-261-41WQ
(METAL)
MN-221-025-261-41WQ
(PLASTIC)



DIMENSIONS									
Size	Contact Row	A	B		C	D	E	H	Hardware
			Plug MAX	RCPT MAX			Potting Well MAX		
9	2	0.775	0.334	0.400	0.390	0.565	0.270	0.298	#2-56 UNC THD (0.092 DIA THROUGH)
15		0.925	0.484	0.550	0.540	0.715			
21		1.075	0.634	0.700	0.690	0.865			
25		1.175	0.734	0.800	0.790	0.965			
31		1.325	0.884	0.950	0.940	1.115			
37		1.475	1.034	1.100	1.090	1.265			
51*		1.825	1.384	1.450	1.440	1.615			

* = 51 Position connectors are available in metal only.