




CARD EDGE MOUNT-TO-CABLE

MK - RUGGED CARD EDGE MOUNT &
MM - RUGGED METAL
0.050" | 9 THROUGH 100 CONTACTS

MK-2G2-037-275-460S
(METAL)



MM-212-037-161-22WQ
(METAL)



DIMENSIONS												
Size	Contact Row	A	B		C	D	E	H	Hardware	Mounting Holes	R	S
			Plug MAX	RCPT MAX			Potting Well MAX					
9	2	0.775	0.334	0.400	0.390	0.565	0.270	0.298	#2-56 UNC THD	#4-40 UNC THD	0.355	0.519
15		0.925	0.484	0.550	0.540	0.715					0.505	
21		1.075	0.634	0.700	0.690	0.865					0.655	
25		1.175	0.734	0.800	0.790	0.965					0.755	
31		1.325	0.884	0.950	0.940	1.115					0.905	
37		1.475	1.034	1.100	1.090	1.265					1.055	
51	3	1.425	0.984	1.050	1.040	1.215	0.310	0.341	#4-40 UNC THD	#4-40 UNC THD	1.005	0.540
69		1.725	1.284	1.350	1.340	1.515					1.309	
100		4	2.160	1.384	1.508	1.432					1.800	