


CABLE-TO-CABLE HYBRID

MM – RUGGED METAL
0.050" | 7 THROUGH 24 CONTACTS



DIMENSIONS									
Size	Contact Row	A	B		C	D	E	H	Hardware
			Plug MAX	RCPT MAX			Potting Well MAX		
7	2	1.175	0.734	0.800	0.790	0.965	0.270	0.298	#2-56 UNC THD (0.092 DIA THROUGH)
24	3	1.425	0.984	1.050	1.040	1.215	0.310	0.341	