



RUGGED METAL I/O (SEALED CONNECTOR)

MM
0.050" | 9 THROUGH 100 CONTACTS


MATING MATRIX	
Connector	Mates With
MM-2E...	MK, ML, MM, MN receptacles
MM-2H...	MK, ML, MM, MN plugs
MM-2K...	MK, ML, MM, MN receptacles
MM-2L...	MK, ML, MM, MN plugs





MM-2E2-031-161-26WA
(PLUG)




MM-2H2-031-261-26WA
(RECEPTACLE)



STRANDED WIRE TERMINATION
(PLUG SHOWN)



SOLDER CUP OR PIGTAIL TERMINATION
(PLUG WITH SOLDER CUP TERMINATION SHOWN)



DIMENSIONS																
Size	Contact Row	A		B		C	Hardware	D	E	F	G	H	J		K	
		Plug MAX	RCPT MAX	Plug MAX	RCPT MAX								Plug	RCPT	Plug	RCPT
9	2	0.185	0.251	0.334	0.400	0.565	2-56 UNC THD	0.957	0.480	0.773	0.298	0.210	0.183	0.195	0.598	0.610
15				0.484	0.550	0.715		1.107		0.923						
21				0.634	0.700	0.865		1.257		1.073						
25				0.734	0.800	0.965		1.357		1.173						
31				0.884	0.950	1.115		1.507		1.323						
37				1.034	1.100	1.265		1.657		1.473						
51	3	0.228	0.294	0.984	1.050	1.215	#4-40 UNC THD	1.657	0.523	1.477	0.440	0.239				
69				1.284	1.350	1.515		1.957		1.777						
100	4	0.271	0.394	1.384	1.508	1.800	#4-40 UNC THD	2.383	0.600	2.219	0.515	0.301				

** Shell accepts 0.200 Max #2-56 screw length (0.295 Max #4-40 screw length).