


RIGHT-ANGLE BOARDMOUNT (BLIND-CLEARANCE CUT)



MK
0.050" | 9 THROUGH 100 CONTACTS

MATING MATRIX	
Connector	Mates With
MK-2T...	MK, ML, MM, MN receptacles
MK-2V..	MK, ML, MM, MN plugs

MK-2T2-031-335-2205
(PLUG)



MK-2V2-031-445-2205
(RCPT)



DIMENSIONS																				
Size	Contact Row	A	B		C		D	F	H	J		K	W	X MAX	Y MAX	Z	Hardware	Mounting Hole		
			Plug MAX	RCPT MAX	Plug MAX	RCPT MAX				Plug	RCPT									
9	2	0.775	0.334	0.400	0.185	0.251	0.565	0.020	0.298	0.183	0.195	0.067	0.250	0.420	0.420	0.775	#2-56 UNC THD	0.096 DIA or #2-56 UNC Threaded Insert		
15		0.925	0.484	0.550			0.715	0.120								0.925				
21		1.075	0.634	0.700			0.865									1.075				
25		1.175	0.734	0.800			0.965									1.175				
31		1.325	0.884	0.950			1.115							0.450	0.520	1.080				
37		1.475	1.034	1.100			1.265	1.180												
51	3	1.425	0.984	1.050	0.228	0.294	1.215	0.150	0.341	0.183	0.195	0.087	0.300	0.430	0.650	1.220				
69		1.725	1.284	1.350			1.515								0.755	1.450				
100	4	2.160	1.384	1.508	0.271	0.394	1.800	0.200	0.384			0.137	0.400	0.590	1.000	1.810	#4-40 UNC THD	0.125 DIA #2-56 UNC Insert #4-40 UNC Insert		