



1 ROW CABLE-TO-CABLE RUGGED METAL I/O CONNECTORS

MM
0.050" | 4 THROUGH 25 CONTACTS


MATING MATRIX	
Connector	Mates With
MM-11..	MM-12, MK-16, MK-18 receptacles
MM-12...	MM-11, MK-15, MK-17 plugs



MM-112-015-161-41WO
(PLUG)



MM-122-015-261-22WO
(RECEPTACLE)



DIMENSIONS										
Size	A	B	C		D	E		F		Hardware
			Plug MAX	RCPT MAX		Plug MAX	RCPT MAX	Plug MAX	RCPT MAX	
4	0.655	0.475	0.260	0.297	0.297	.186	0.198	0.358	0.370	#2-56 UNC THD (0.092 DIA THROUGH)
5	0.705	0.525	0.310	0.347	0.347					
6	0.755	0.575	0.360	0.397	0.397					
9	0.905	0.725	0.510	0.547	0.547					
12	1.055	0.875	0.660	0.697	0.697					
15	1.205	1.025	0.810	0.847	0.847					
21	1.505	1.325	1.110	1.147	1.147					
25	1.705	1.525	1.310	1.347	1.347					