



HORIZONTAL SURFACE MOUNT (1-ROW)

MK
0.050" | 4 THROUGH 25 CONTACTS



MATING MATRIX	
Connector	Mates With
MK-17...	MM-12, MK-18 receptacles
MK-18...	MM-11, MK-17 plugs



MK-172-009-175-220S
(PLUG)



MK-182-009-275-410S
(RECEPTACLE)



2X #2-56 JACKPOST
SEE PAGE 209

PLUG SHOWN

DIMENSIONS											
Size	A	B		C	D	E	F		G		Mounting Hole
		Plug MAX	RCPT MAX				Plug MAX	RCPT MAX	Plug MAX	RCPT MAX	
4	0.655	0.260	0.297	0.475	0.265	0.460	0.110	0.142	0.186	0.198	#2-56 Threaded Through
5	0.705	0.310	0.347	0.525	0.315	0.510					
6	0.755	0.360	0.397	0.575	0.365	0.560					
9	0.905	0.510	0.547	0.725	0.515	0.710					
12	1.055	0.660	0.697	0.875	0.665	0.860					
15	1.205	0.810	0.847	1.025	0.815	1.010					
21	1.505	1.110	1.147	1.325	1.115	1.310					
25	1.705	1.310	1.347	1.525	1.315	1.510					