



CONNECTOR SAVER

MM – RUGGED METAL &
MN – RUGGED PLASTIC
0.050" | 9 THROUGH 100 CONTACTS

MM-212-031-143-2200-93A
(METAL)
MN-211-031-143-2200-93A
(PLASTIC)



DIMENSIONS							
Size	Contact Row	A	B		D	H	Hardware
			Plug MAX	RCPT MAX			
9	2	0.775	0.334	0.400	0.565	0.298	#2-56 UNC THD (0.092 DIA Through)
15		0.925	0.484	0.550	0.715		
21		1.075	0.634	0.700	0.865		
25		1.175	0.734	0.800	0.965		
31		1.325	0.884	0.950	1.115		
37		1.475	1.034	1.100	1.265		
51**		1.825	1.384	1.450	1.615		
51	3	1.425	0.984	1.050	1.215	0.341	#4-40 UNC THD (0.147 DIA Through)
69***		1.725	1.284	1.350	1.515		
100	4	2.160	1.384	1.508	1.800	0.384	#4-40 UNC THD (0.147 DIA Through)

*** 69 Position connectors are available in metal only.
** Two row, 51 position connectors are available in metal only, (non MIL-SPEC interface).