


EMI/RFI 45° BACKSHELLS

MM – RUGGED METAL
0.050" | 9 THROUGH 100 CONTACTS



MM 45° (ONE PIECE)

DIMENSIONS													
Size	Contact Row	A	B	C	D	E	F	H	J	K	L	M	Hardware
9	2	0.775	0.440	0.340	0.565	0.696	0.500	0.298	0.229	0.804	—	0.188	#2-56 UNC THD (0.092 DIA Through)
15		0.925	0.590		0.715	0.721	0.525			0.954	—	0.230	
21		1.075	0.740		0.865	0.746	0.550			1.103	—	0.257	
25		1.175	0.840		0.965	0.796	0.600			1.203	0.265	0.310	
31		1.325	0.990		1.115	0.846	0.650			1.353		0.330	
37		1.475	1.140		1.265	0.921	0.725			1.503		0.375	
51		1.825	1.490		1.615	1.144	0.950			1.853		0.510	
51	3	1.425	1.090	0.380	1.215	0.946	0.750	0.341		1.453	0.297	0.470	
69		1.725	1.390		1.515					1.753		0.620	
100	4	2.160	1.522	0.430	1.800	1.146	0.950	0.384			2.036	0.344	0.688

MM 45° (TWO PIECE)

DIMENSIONS														
Size	Contact Row	A	B	C	D	E	F	H	J	K	L	M	Hardware	
9	2	0.775	0.480	0.340	0.565	0.855	0.650	0.298	0.229	0.806	—	0.188	#2-56 UNC THD (0.092 DIA Through)	
15		0.925	0.630		0.715	0.831	0.625			0.944	—	0.230		
21		1.075	0.780		0.865	0.985	0.421			1.059	0.240	0.268		
25		1.175	0.880		0.965	1.031	0.400			1.159		0.333		
31		1.325	1.030		1.115	1.046				1.309		0.354		
37		1.475	1.180		1.265	1.081				1.459		0.404		
51		1.825	1.530		1.615	1.193				1.809		0.559		
51	3	1.425	1.130	0.380	1.215	1.233	0.625	0.341		1.409	0.280	0.492		#4-40 UNC THD (0.147 DIA Through)
69		1.725	1.430		1.515	1.378	0.527			1.703		0.642		
100	4	2.160	1.522	0.430	1.800	1.403	0.532	0.384		1.973	0.330	0.711		