


CABLE-TO-CABLE

MMHT – RUGGED METAL HIGH TEMPERATURE 0.050" | 9 THROUGH 100 CONTACTS



DIMENSIONS									
Size	Contact Row	A	B		C	D	E	H	Hardware
			Plug MAX	RCPT MAX			Potting Well MAX		
9	2	0.775	0.334	0.400	0.390	0.565	0.270	0.298	#2-56 UNC THD (0.092 DIA THROUGH)
15		0.925	0.484	0.550	0.540	0.715			
21		1.075	0.634	0.700	0.690	0.865			
25		1.175	0.734	0.800	0.790	0.965			
31		1.325	0.884	0.950	0.940	1.115			
37		1.475	1.034	1.100	1.090	1.265			
51	3	1.425	0.984	1.050	1.040	1.215	0.310	0.341	#4-40 UNC THD (0.147 DIA THROUGH)
100	4	2.160	1.384	1.508	1.432	1.800	0.360	0.384	