


CABLE-TO-CABLE

MQHT - LOW-PROFILE METAL HIGH TEMPERATURE 0.050" | 9 THROUGH 51 CONTACTS



DIMENSIONS									
Size	Contact Row	A	B		C	D	E	H	Hardware
			Plug MAX	RCPT MAX			Potting Well MAX		
9	2	0.778	0.292	0.378	0.398	0.565	0.173	0.208	#2-56 UNC THD (0.092 DIA THROUGH)
15		0.928	0.442	0.528	0.548	0.715			
21		1.078	0.592	0.678	0.698	0.865			
25		1.178	0.692	0.778	0.798	0.965			
31		1.328	0.842	0.928	0.948	1.115			
37	3	1.478	0.992	1.078	1.098	1.265	0.220	0.250	#2-56 UNC THD (0.092 DIA THROUGH)
51		1.428	0.942	1.028	1.048	1.215			