





CABLE-TO-BOARD

MTHT – LOW-PROFILE CABLE HIGH TEMPERATURE &
MTHT – LOW-PROFILE BOARD MOUNT
HIGH TEMPERATURE
0.050" | 9 THROUGH 51 CONTACTS


MTHT-212-021-161-43WQ
(METAL)



MTHT-2E2-021-433-000S
(METAL)



SEE PAGE 209



PLUG

RECEPTACLE

DIMENSIONS												
Size	Contact Row	A	B		C	D	E	F	H	Hardware	W	Y
			Plug MAX	RCPT MAX			Potting Well MAX					
9	2	0.778	0.292	0.378	0.398	0.565	0.173	0.600	0.208	#2-56 UNC THD (0.092 DIA Through)	0.608	0.690
15		0.928	0.442	0.528	0.548	0.715		0.750				
21		1.078	0.592	0.678	0.698	0.865		0.900				
25		1.178	0.692	0.778	0.798	0.965		1.000				
31		1.328	0.842	0.928	0.948	1.115		1.150				
37		1.478	0.992	1.078	1.098	1.265		1.300				
51	3	1.428	0.942	1.028	1.048	1.215	0.220	1.250	0.250		0.728	0.825