


BOARD-TO-CABLE (NARROW FOOTPRINT)

MSHT - LOW-PROFILE BOARD MOUNT HIGH TEMPERATURE & MQHT - LOW-PROFILE CABLE HIGH TEMPERATURE
 0.050" | 9 THROUGH 51 CONTACTS



DIMENSIONS														
Size	Contact Row	A	B		C	D	E	F	H	W	X MAX	X MAX	Z	Hardware
			Plug MAX	RCPT MAX										
9	2	0.778	0.292	0.378	0.398	0.565	0.173	0.020	0.208	0.250	0.420	0.420	0.775	#2-56 UNC THD
15		0.928	0.442	0.528	0.548	0.715							0.925	
21		1.078	0.592	0.678	0.698	0.865							1.075	
25		1.178	0.692	0.778	0.798	0.965							1.175	
31		1.328	0.842	0.928	0.948	1.115							1.080	
37		1.478	0.992	1.078	1.098	1.265							1.180	
51	3	1.428	0.942	1.028	1.048	1.215	0.220	0.150	0.250	0.300	0.425	0.650	1.220	