



TWO ROW – CABLE-TO-BOARD RIGHT ANGLE PTH


NM & NK
0.025" | 9 THROUGH 91 CONTACTS



SIZE	A	B	C		D	E	F	G	H	J	*HARDWARE
			PLUG	RCPT							
9	.375	.270	.160	.163	.170						
15	.450	.345	.235	.238	.245						
21	.525	.420	.310	.313	.320						
25	.575	.470	.360	.363	.370						
31	.650	.545	.435	.438	.445	.125	.345	.187	.018	.0575	#0-80 THREAD
37	.725	.620	.510	.513	.520						
51	.900	.795	.685	.688	.695						
65	1.075	.970	.860	.863	.870						
69	1.125	1.020	.910	.913	.920						
85	1.377	1.246	1.110	1.113	1.120	.150	.410	.244	.075	.0700	#2-56 THREAD
91	1.452	1.321	1.185	1.188	1.195						



PIN CONTACT
3 TINE SPRING MEMBER, CRIMP



SOCKET CONTACT
DRAWN TUBE, CRIMP

* = #2-56 UNC THREAD ON 85 AND 91 POSITION CONNECTORS.
** = 1/16" HEX ON 85 AND 91 POSITION CONNECTORS. HEX MEASUREMENT
TAKEN ACROSS THE FLATS.
*** = OTHER LENGTHS AS REQUIRED