



TWO ROW – FLEX-TO-BOARD

NM & NK
0.025" | 9 THROUGH 91 CONTACTS



DIMENSIONS									
SIZE	A	B	C		D	E	F		*HARDWARE
			PLUG	RCPT			PLUG	RCPT	
9	.375	.270	.160	.163	.170	.125	.330	.225	#0-80 THREAD
15	.450	.345	.235	.238	.245				
21	.525	.420	.310	.313	.320				
25	.575	.470	.360	.363	.370				
31	.650	.545	.435	.438	.445				
37	.725	.620	.510	.513	.520				
51	.900	.795	.685	.688	.695				
65	1.075	.970	.860	.863	.870				
69	1.125	1.020	.910	.913	.920				
85	1.377	1.246	1.110	1.113	1.120	.150		.0700	#2-56 THREAD
91	1.452	1.321	1.185	1.188	1.195				



* = #2-56 UNC THREAD ON 85, 91 POSITION CONNECTORS.
** = 1/16" HEX ON 85 POSITION CONNECTORS. HEX MEASUREMENT TAKEN ACROSS THE FLATS.
*** = OTHER LENGTHS AS REQUIRED