




0.025" | 9 THROUGH 91 CONTACTS



DIMENSIONS										
SIZE	A	B	C		D	E	J	AA	BB	HARDWARE*
			PLUG	RCPT						
9	.375	.270	.160	.163	.170	.125	.0575	.625	.520	#0-80 THREAD
15	.450	.345	.235	.238	.245			.700	.595	
21	.525	.420	.310	.313	.320			.775	.670	
25	.575	.470	.360	.363	.370			.825	.720	
31	.650	.545	.435	.438	.445			.900	.795	
37	.725	.620	.510	.513	.520			.975	.870	
51	.900	.795	.685	.688	.695			1.150	1.045	
65	1.075	.970	.860	.863	.870			1.325	1.220	
69	1.125	1.020	.910	.913	.920	1.375	1.270	#2-56 THREAD		
85	1.377	1.246	1.110	1.113	1.120	1.679	1.546			
91	1.452	1.321	1.185	1.188	1.195	1.754	1.625			



PIN CONTACT
3 TINE SPRING MEMBER,
CRIMP



SOCKET CONTACT
DRAWN TUBE, CRIMP

* = #2-56 UNC THREAD ON 85 & 91 POSITION CONNECTORS
 ** = DIMENSION CHANGES TO .040" FOR "010" OPTION.
 SEE PAGE N-61.