






TWO ROW – REAR PANEL MOUNT HORIZONTAL SMT

NKRP
0.025" | 9 THROUGH 85 CONTACTS



RECEPTACLE



DIMENSIONS											
SIZE	A	B	C	D	E	J	L	M	N	P	R
9	.890	.566	.270	.163	.390	.190	.688	.405	.215	.255	.531
15	.965	.641	.345	.238			.763	.480			.606
21	1.040	.716	.420	.313			.838	.555			.681
25	1.090	.766	.470	.363			.888	.605			.731
31	1.165	.841	.545	.438			.963	.680			.806
37	1.240	.916	.620	.513			1.038	.755			.881
51	1.415	1.091	.795	.688			1.213	.930			1.056
65	1.590	1.266	.970	.863			1.388	1.105			1.231
69	1.640	1.316	1.020	.913	.415	.2025	1.438	1.155	.244	.300	1.281
85	1.892	1.568	1.246	1.113			1.690	1.407			1.533

* = #2-56 UNC THREAD ON 85 & 91 POSITION CONNECTORS.