



TWO ROW – HORIZONTAL SMT PLUG WITH JACKSCREWS

NK
0.025" | 9 THROUGH 91 CONTACTS



NK-2C2-025-125-JC00
(METAL)



PIN CONTACT
3 TINE SPRING MEMBER, CRIMP

DIMENSIONS											
SIZE	A	B	C	D	E	F	G	J	K	L	*HARDWARE
9	.375	.270	.160	.170	.125	.205	.535	.0575	.435	.100	#0-80 THREAD
15	.450	.345	.235	.245			.610		.510		
21	.525	.420	.310	.320			.685		.585		
25	.575	.470	.360	.370			.735		.635		
31	.650	.545	.435	.445			.810		.710		
37	.725	.620	.510	.520			.885		.785		
51	.900	.795	.685	.695			1.060		.960		
65	1.075	.970	.860	.870			1.235		1.135		
69	1.125	1.020	.910	.920	.150	.192	1.285	.0700	1.185	.126	#2-56 THREAD
85	1.377	1.246	1.110	1.120			1.590		1.463		
91	1.452	1.321	1.185	1.195			1.665		1.538		