




TWO ROW – VERTICAL PTH PLUG WITH TURNING HARDWARE AND MOUNTING EARS

NK
0.025" | 9 THROUGH 91 CONTACTS




PIN CONTACT
3 TINE SPRING MEMBER, CRIMP

DIMENSIONS									
SIZE	A	B	AA	BB	C	D	E	J	*HARDWARE
9	.375	.270	.625	.520	.160	.170	.125	.0575	#0-80 THREAD
15	.450	.345	.700	.595	.235	.245			
21	.525	.420	.775	.670	.310	.320			
25	.575	.470	.825	.720	.360	.370			
31	.650	.545	.900	.795	.435	.445			
37	.725	.620	.975	.870	.510	.520			
51	.900	.795	1.150	1.045	.685	.695			
65	1.075	.970	1.325	1.220	.860	.870			
69	1.125	1.020	1.375	1.270	.910	.920			
85	1.377	1.246	1.679	1.546	1.110	1.120			
91	1.452	1.321	1.754	1.621	1.185	1.195	.150	.070	#2-56 THREAD

* = #2-56 UNC THREAD ON 85 & 91 POSITION CONNECTORS.

** = OTHER LENGTHS AS REQUIRED

*** = 1/16" HEX ON 85 & 91 POSITION CONNECTORS.
HEX MEASUREMENT TAKEN ACROSS THE FLATS.



SOCKET CONTACT
DRAWN TUBE, CRIMP