




DIMENSIONS



ISOMETRIC VIEW
FOR REFERENCE ONLY

COLUMNS	A	B	C	ROWS	D
10	1.222	0.813	0.450	4	0.470
20	1.722	1.313	0.950	5	0.520
30	2.222	1.813	1.450	6	0.570
40	2.722	2.313	1.950	8	0.670
50	3.222	2.813	2.450	10	0.770

LENGTH		
CODE	LENGTH (M)	LENGTH (IN)
010	0.10	3.94
020	0.20	7.87
030	0.30	11.81
040	0.40	15.75
050	0.50	19.69
060	0.60	23.62
070	0.70	27.56
080	0.80	31.50
090	0.90	35.43
100	1.00	39.37
150	1.50	59.06
200	2.00	78.74
300	3.00	118.11

Please consult the Molex website for the latest revision of this document prior to beginning any design work.