

LEAD CONFIGURATION OPTIONS

PLUGS		RECEPTACLES	
SERIES			
MM	0.050" " Rugged Metal I/O Connector (MM mates to MK and MM)	MM	0.050" Rugged Metal I/O Connector (MM mates to MK and MM)
BODY			
1	1-Row (Sizes 4 through 25)	1	1-Row (Sizes 4 through 25)
BODY STYLE		BODY STYLE	
1	Plug, straight	2	Receptacle, straight
BODY MATERIAL		BODY MATERIAL	
2	Electroless Ni shell with PPS insert	2	Electroless Ni shell with PPS insert
3	Electrodeposited cadmium shell with PPS insert [x]	3	Electrodeposited cadmium shell with PPS insert [x]
5	Stainless Steel shell with PPS insert	5	Stainless Steel shell with PPS insert
A	Pure Electrodeposited Aluminum	A	Pure Electrodeposited Aluminum
K	Zinc nickel plating	K	Zinc nickel plating
T	Nickel polymer plating	T	Nickel polymer plating
SIZE			
XXX	004, 005, 006, 009, 012, 015, 021, 025	XXX	004, 005, 006, 009, 012, 015, 021, 025
CONTACTS			
TYPE CONTACTS/TERMINATIONS		TYPE CONTACTS/TERMINATIONS	
11	Pin, straight, 26 AWG solder cup	21	Socket, straight, 26 AWG solder cup
1A	Pin, straight, 24 AWG solder cup	2A	Socket, straight, 24 AWG solder cup
12	Pin, straight, 0.150" pigtails (0.018 dia.)	22	Socket, straight, 0.150" pigtails (0.018 dia.)
13	Pin, straight, 0.250" pigtails (0.018 dia.)	23	Socket, straight, 0.250" pigtails (0.018 dia.)
14	Pin, straight, 0.500" pigtails (0.018 dia.)	24	Socket, straight, 0.500" pigtails (0.018 dia.)
16	Pin, straight, crimped wire	26	Socket, straight, crimped wire
PLATING OPTIONS		PLATING OPTIONS	
1	50 µm Au contacts (crimped wire)	1	50 µm Au contacts (crimped wire)
3	50 µm Au contacts: Au terminations (solder cup, pigtail)	3	50 µm Au contacts: Au terminations (solder cup, pigtail)
5	50 µm Au contacts: Sn/Pb alloy terminations (pigtail) [x]	5	50 µm Au contacts: Sn/Pb alloy terminations (pigtail) [x]
7	50 µm Au contacts: SAC305 terminations (pigtail)	7	50 µm Au contacts: SAC305 terminations (pigtail)
HARDWARE			
STYLE OF HARDWARE		STYLE OF HARDWARE	
00	None	00	None
22	Two fixed jacknut assemblies	22	Two fixed jacknut assemblies
41	Two turning jackscrews, Allen head, retaining ring	41	Two turning jackscrews, Allen head, retaining ring
45	Two turning jackscrews, Allen head, captivated**	45	Two turning jackscrews, Allen head, captivated**
WIRING		WIRING	
XX	For wiring codes, see pages M-158 and M-159.	XX	For wiring codes, see pages M-158 and M-159.
OPTIONS			
		900	Interfacial Seal

PLUG: MM-112-006-113-2200
RECEPTACLE: MM-122-006-2A3-4100



NOTE:

** Captive hardware is factory installed and non-removable. .

[x] Option is not RoHS-compliant