

LEAD CONFIGURATION OPTIONS

RUGGED:

MM-272- 031-000- 4100
XX-XXX-XXX-XXX-XXXX

SERIES

MM .050" Rugged Metal Backshell

BODY

2 2-Row (Sizes 9 thru 51)

3 3-Row (Sizes 51 & 69)

4 4-Row (Size 100)

BODY STYLE:

7 90°, one piece

BODY MATERIAL:

2 Aluminum, with electroless nickel plating

3 Aluminum, with electrodeposited cadmium ☒

4 Aluminum, with hard anodized black plating

SIZE

XXX 009, 015, 021, 025, 031, 037, 051, 069, 100

EXIT

000 Standard exit**

HARDWARE

STYLE OF HARDWARE:

00 None

22 Two fixed jacknut assemblies (62*)

41 Two turning jackscrews, allen head, retaining ring (81*)

43 Two turning jackscrews, slot head, retaining ring (83*)

44 Two long turning jackscrews, slot head, retaining ring (84*)

POLARIZATION / WIRING:

00 None

* = Use number in parenthesis when ordering size 100.

** = Backshell exits are designed to accomodate 26AWG wire or smaller

Stainless steel micro band for shield termination - AirBorn part number CDG10026, shipped with each backshell

Band-it application tool - AirBorn part number CDG10027

☒ = Option not ROHS compliant