

LEAD CONFIGURATION OPTIONS

PLUG COVER: ND-1P2-009-JC
RECEPTACLE COVER: ND-1R2-009-TH
XX-XXX-XXX-XX

PLUG COVER		RECEPTACLE COVER	
SERIES			
ND .025" Metal Dust Cover		ND .025" Metal Dust Cover	
BODY			
1 1-Row		1 1-Row	
P BODY STYLE: Plug cover		R BODY STYLE: Receptacle cover	
2 BODY PLATING: Electroless nickel		2 BODY PLATING: Electroless nickel	
3 Electrodeposited cadmium ☒		3 Electrodeposited cadmium ☒	
SIZE			
XXX 009, 015, 021, 025, 031, 037 or 051		XXX 009, 015, 021, 025, 031, 037 or 051	
HARDWARE			
JC STYLE OF HARDWARE: Turning jackscrews, captivated #0-80 UNF*		JC STYLE OF HARDWARE: Turning jackscrews, captivated #0-80 UNF*	
TH Threaded hole, #0-80 UNF		TH Threaded hole, #0-80 UNF	

* = Recommended torque value 1.0 inch-lbs. max.
Ball end hex wrench not recommended
Hex wrench key/bit conforming to the requirements of ASME / ANSI-B-18.3 is recommended.
.050" hex L-key long arm wrench - order AirBorn p/n CDG14148.

☒ = Option not RoHS compliant