



PLUG: WBB50PMT
 RECEPTACLE: WB50SD6
 XXXXXXXXXXXXX

PLUG

RECEPTACLE

SERIES

| | |
|--|--|
| WBB 2 row, SMT, plug, with mounting ears | WB 2 row, straight, receptacle, with mounting ears |
| WBA 2 row, SMT, plug, full skirt, with mounting ears | |

SIZE

| | |
|--|--|
| 20, 30, 40, 50, 60, 70, 80, 90, 100, 110, 128, 132 | 20, 30, 40, 50, 60, 70, 80, 90, 100, 110, 128, 132 |
|--|--|

CONTACTS

| | |
|--|---|
| TYPE CONTACTS/TERMINATIONS: PMT Pin, card edge SMT (Board: .054/.070) | TYPE CONTACTS/TERMINATIONS: SD6 Socket, straight, dip solder, .095" SD9 Socket, straight, dip solder, .140" SD12 Socket, straight, dip solder, .190" SD19 Socket, straight, dip solder, .300" |
|--|---|

HARDWARE

| | |
|---|--|
| STYLE OF HARDWARE: (See WB-9) K*_* Integral keying guides, polarized KY*_* Stainless steel keying guides, polarized JMM 2 stainless steel fixed jackscrews | STYLE OF HARDWARE: (See WB-9) K*_* Integral keying guides, polarized KY*_* Stainless steel keying guides, polarized JTFF 2 stainless steel turning jackscrews |
|---|--|

| DIMENSIONS | | | | | |
|------------|-------|-------|-------|-------|-------|
| SIZE | A | B | C | D | E |
| 20 | 1.150 | .900 | .450 | 1.030 | .750 |
| 30 | 1.400 | 1.150 | .700 | 1.280 | 1.000 |
| 40 | 1.650 | 1.400 | .950 | 1.530 | 1.250 |
| 50 | 1.900 | 1.650 | 1.200 | 1.780 | 1.500 |
| 60 | 2.150 | 1.900 | 1.450 | 2.030 | 1.750 |
| 70 | 2.400 | 2.150 | 1.700 | 2.280 | 2.000 |
| 80 | 2.650 | 2.400 | 1.950 | 2.530 | 2.250 |
| 90 | 2.900 | 2.650 | 2.200 | 2.780 | 2.500 |
| 100 | 3.150 | 2.900 | 2.450 | 3.030 | 2.750 |
| 110 | 3.400 | 3.150 | 2.700 | 3.280 | 3.000 |
| 128 | 3.850 | 3.600 | 3.150 | 3.730 | 3.450 |
| 132 | 3.950 | 3.700 | 3.250 | 3.830 | 3.550 |