


Double-Crimp Terminals >

Product Family	Part Number	Description	Wire Size (AWG)*
<u>Mini-Fit</u> 	39000077	Mini-Fit Sr. female crimp terminal	18+22, 20+20, 20+22
	39000079	Mini-Fit Sr. female crimp terminal	18+22, 20+20, 20+22
	39000038	Mini-Fit Sr. female crimp terminal	22+22
	39000059	Mini-Fit female crimp terminal	22+22
	39000081	Mini-Fit male crimp terminal	18+22, 20+20, 20+22
	39000083	Mini-Fit male crimp terminal	18+22, 20+20, 20+22
	39000040	Mini-Fit male crimp terminal	22+22
	39000061	Mini-Fit male crimp terminal	22+22
<u>Mini-Fit Sigma</u> 	1727184111	Mini-Fit TPA2/Sigma female crimp terminal	22+22
	1727184121	Mini-Fit TPA2/Sigma female crimp terminal	22+22
	1727654121	Mini-Fit TPA2/Sigma male crimp terminal	22+22
	2029884141	Mini-Fit TPA2/Sigma female crimp terminal	22+22
	2029884241	Mini-Fit TPA2/Sigma female crimp terminal	22+22
<u>VersaBlade</u> 	357450310	VersaBlade male crimp terminal	18+18, 20+20
	357460310	VersaBlade female crimp terminal	18+18, 20+20
	357470310	VersaBlade male crimp terminal	18+18, 20+20
	357480310	VersaBlade female crimp terminal	18+18, 20+20
	2173478200	VersaBlade high-temperature male crimp terminal	18+18, 20+20, 18+20
	2173488200	VersaBlade high-temperature female crimp terminal	18+18, 20+20, 18+20
<u>Sabre</u> 	433751001	Sabre double-crimp terminal, female	18+18
	433745001	Sabre double-crimp terminal, female	20+20
	433755001	Sabre double-crimp terminal, female	20+20
	431782001	Sabre double-crimp terminal, male	18+20
	431783001	Sabre double-crimp terminal, male	18+18
	431782002	Sabre double-crimp terminal, male	18+20
	431786002	Sabre double-crimp terminal, male	18+20
<u>Pin and Socket Connectors</u> 	2098108	Standard .093" Pin and Socket Connectors	16+18, 18+18

Double-Crimp Terminals >

Product Family	Part Number	Description	Wire Size*
<u>Mini-Fit Sr.</u> 	428150134	Mini-Fit Sr. female crimp terminal	12+12
	428150032	Mini-Fit Sr. female crimp terminal	12+12
	428171034	Mini-Fit Sr. male crimp terminal	12+12
	428171134	Mini-Fit Sr. male crimp terminal	12+12
	428170032	Mini-Fit Sr. male crimp terminal	12+12
	428170132	Mini-Fit Sr. male crimp terminal	12+12
<u>Mega-Fit</u> 	768230343	Tangless TPA-capable crimp terminal, female	16+16
	768230344	Tangless TPA-capable crimp terminal, female	18+18, 20+20
	1720630333	Mega-Fit Tangless TPA-capable crimp terminal, female	16+16
	1720630334	Mega-Fit Tangless TPA-capable crimp terminal, female	18+18, 20+20
	1720631333	Tangless TPA-capable crimp terminal, female	16+16
	1720631334	Tangless TPA-capable crimp terminal, female	18+18, 20+20
	1054170333	Mega-Fit crimp terminal, male	16+16
	1054170334	Mega-Fit crimp terminal, male	18+18, 20+20
	1054180313	Mega-Fit crimp terminal, male	16+16
	1054180314	Mega-Fit crimp terminal, male	18+18, 20+20
	1054181313	Mega-Fit crimp terminal, male	16+16
<u>Micro-Fit</u> 	43030-0001	Micro-Fit 3.0 crimp terminal, female, tin plated	24+24, 26+26
	43030-0002	Micro-Fit 3.0 crimp terminal, female, select gold plated	24+24, 26+26
	43030-0003	Micro-Fit 3.0 crimp terminal, female, select gold plated	24+24, 26+26
	43030-0051	Micro-Fit 3.0 crimp terminal, female	24+24, 26+26
	43030-0052	Micro-Fit 3.0 crimp terminal, female	24+24, 26+26
	43030-0053	Micro-Fit 3.0 crimp terminal, female	24+24, 26+26
	43031-0001	Micro-Fit 3.0 crimp terminal, male, tin plated	24+24, 26+26
	43031-0002	Micro-Fit 3.0 crimp terminal, male, select gold plated	24+24, 26+26
	43031-0003	Micro-Fit 3.0 crimp terminal, male, select gold plated	24+24, 26+26
	43031-0017	Micro-Fit 3.0 crimp terminal, male	24+24, 26+26
	43031-0103	Micro-Fit 3.0 crimp terminal, male	24+24, 26+26

*Noted wire sizes are supported within the product families listed. For applicable insulation diameter, refer to Molex.com for each contact part number in the Application Tooling Specification (ATS).