

TWO ROW – STRIP CONNECTORS BOARD-TO-CABLE

MA-2

0.050" | 4 THROUGH 128 CONTACTS

DIMENSIONS

To determine connector length (Dim "A"):

Multiply the number of cavities in one row by .050"

Add fixed end lengths (constant, .025" x 2)

Add .085" for each mounting hole

Total Length:

0.050"

Notes:

Length over 2" may require support to insure alignment





* = Maximum length is 3.420". Maximum number of contacts must be reduced to accommodate hardware and mounting holes.

** = For cable applications, .295" becomes .390"

*** = For solder cup or board mount applications, .230" becomes .135"

MA-2F1-010-325-A5200

MA-241-010-261-A53WA



OPTIONAL MOUNTING HOLES