



TWO ROW – VERTICAL PTH PLUG WITH TURNING HARDWARE

NK
0.025" | 9 THROUGH 91




NK-2G2-025-135-JC00
PLUG



DIMENSIONS							
SIZE	A	B	C	D	E	J	*HARDWARE
9	.375	.270	.160	.170	.125	.0575	#0-80 THREAD
15	.450	.345	.235	.245			
21	.525	.420	.310	.320			
25	.575	.470	.360	.370			
31	.650	.545	.435	.445			
37	.725	.620	.510	.520			
51	.900	.795	.685	.695			
65	1.075	.970	.860	.870			
69	1.125	1.020	.910	.920			
85	1.377	1.246	1.110	1.120			
91	1.452	1.321	1.185	1.195	.150	.070	#2-56 THREAD



PIN CONTACT
3 TINE SPRING MEMBER, CRIMP



SOCKET CONTACT
DRAWN TUBE, CRIMP

* = #2-56 UNC THREAD ON 85 AND 91 POSITION CONNECTORS.
** = OTHER LENGTHS AS REQUIRED
*** = 1/16" HEX ON 85 & 91 POSITION CONNECTORS.
HEX MEASUREMENT TAKEN ACROSS THE FLATS.