



HARDWARE

PANEL MOUNTING DIMENSIONS FOR RECEPTACLES WITH GROUNDING FINGERS




FRONT PANEL MOUNTING RECEPTACLES WITH GROUNDING FINGERS



DIMENSIONS				
Size	A + 0.004 - 0.000	B + 0.005 - 0.000	C + 0.004 - 0.000	
			MP, MQ, MR, MS MQHT, MSHT	MK, ML, MM, MN MKHT, MMHT
9	0.570	0.400	0.215	0.273
15	0.720	0.550		
21	0.870	0.700		
25	0.970	0.800		
31	1.120	0.950		
37	1.270	1.100		
51	1.220	1.050	0.256	0.311
69	1.520	1.350	—	
100	1.805	1.442	—	0.383

REAR PANEL MOUNTING RECEPTACLES WITH GROUNDING FINGERS



DIMENSIONS				
Size	A + 0.004 - 0.000	B + 0.004 - 0.000	C ± 0.005	C ± 0.005 Thru
9	0.401	0.308	0.565	0.125
15	0.551		0.715	
21	0.701		0.865	
25	0.801		0.965	
31	0.951		1.115	
37	1.101	0.351	1.265	0.160
51	1.051		1.215	
69	1.351		1.515	
100	1.505	0.391	1.800	0.160