



# TWO ROW – VERTICAL PTH RECEPTACLE WITH TURNING HARDWARE


NK  
0.025" | 9 THROUGH 91 CONTACTS



| DIMENSIONS |       |       |       |       |      |       |              |
|------------|-------|-------|-------|-------|------|-------|--------------|
| SIZE       | A     | B     | C     | D     | E    | J     | *HARDWARE    |
| 9          | .375  | .270  | .163  | .170  | .125 | .0575 | #0-80 THREAD |
| 15         | .450  | .345  | .238  | .245  |      |       |              |
| 21         | .525  | .420  | .313  | .320  |      |       |              |
| 25         | .575  | .470  | .363  | .370  |      |       |              |
| 31         | .650  | .545  | .438  | .445  |      |       |              |
| 37         | .725  | .620  | .513  | .520  |      |       |              |
| 51         | .900  | .795  | .688  | .695  |      |       |              |
| 65         | 1.075 | .970  | .863  | .870  |      |       |              |
| 69         | 1.125 | 1.020 | .913  | .920  | .150 | .070  | #2-56 THREAD |
| 85         | 1.377 | 1.246 | 1.113 | 1.120 |      |       |              |
| 91         | 1.452 | 1.321 | 1.188 | 1.195 |      |       |              |



PIN CONTACT  
3 TINE SPRING MEMBER, CRIMP



SOCKET CONTACT  
DRAWN TUBE, CRIMP

\* = #2-56 UNC THREAD ON 85 AND 91 POSITION CONNECTORS.  
\*\* = OTHER LENGTHS AS REQUIRED  
\*\*\* = 1/16" HEX ON 85 & 91 POSITION CONNECTORS.  
HEX MEASUREMENT TAKEN ACROSS THE FLATS.