

LEAD CONFIGURATION OPTIONS

NK-2H2-025-235-TH00
XX-XXX-XXX-XXX-XXXX

SERIES									
NK .025" Metal PC Board Mounted Connector									
BODY									
2	2-Row								
BODY STYLE:									
H	Receptacle, vertical mount, plated thru hole (PTH)								
BODY MATERIAL:									
2	Liquid Crystal Polymer w/ electroless nickel shell								
3	Liquid Crystal Polymer w/ electrodeposited cadmium shell ☒								
4	Liquid Crystal Polymer w/ stainless steel shell								
5	Liquid Crystal Polymer w/ titanium shell								
SIZE									
XXX Number of contacts (009, 015, 021, 025, 031, 037, 051, 065, 069, 085 or 091)									
CONTACTS									
TYPE CONTACTS/TERMINATIONS:									
23	Socket, straight, .109"								
24	Socket, straight, .140"								
25	Socket, straight, .172"								
PLATING OPTIONS:									
5	50 u" Au contacts; Sn/Pb alloy terminations ☒								
8	50 u" Au contacts; Tin plated terminations								
HARDWARE									
STYLE OF HARDWARE:									
00	None								
TH	Threaded hole, #0-80 UNF * **								
WIRING OPTIONS:									
00	None								

* = #2-56 UNC thread on 85 and 91 position connectors

.050 hex key (#0-80 thread)

1/16" hex key (#2-56 thread)

Recommended torque value 1.0 inch-lbs. max. (#0-80 thread)

Recommended torque value 2.0 inch-lbs. max. (#2-56 thread)

Ball end hex wrench not recommended

Hex wrench key/bit conforming to the requirements of ASME / ANSI-B-18.3 is recommended.

.050" hex L-key long arm wrench - order AirBorn p/n CDG14148.

1/16" hex L-key long arm wrench - order AirBorn p/n CDG14160.

** = Threaded hole tapped directly into stainless steel and titanium shells, aluminum shells have stainless steel inserts (as shown on previous page).

☒ = Option not RoHS compliant