

NM-2J2-025-PS1-JTAW
 XX-XXX-XXX-XXX-XXXX

| | |
|--|--|
| SERIES | |
| NM .025" Metal I/O Connector | |
| BODY | |
| 2 | 2-Row |
| BODY STYLE: | |
| J | Jumper assembly |
| BODY MATERIAL: | |
| 2 | Liquid Crystal Polymer with electroless nickel shell |
| 3 | Liquid Crystal Polymer with electrodeposited cadmium shell <input checked="" type="checkbox"/> |
| 4 | Liquid Crystal Polymer with stainless steel shell |
| 5 | Liquid Crystal Polymer with titanium shell |
| SIZE | |
| XXX Number of contacts (009, 015, 021, 025, 031, 037, 051, 065, 069, 085 or 091) | |
| CONTACTS | |
| TYPE CONTACTS/TERMINATIONS: | |
| PP | Plug to plug |
| PS | Plug to receptacle |
| SS | Receptacle to receptacle |
| PLATING OPTIONS: | |
| 1 | 50 μ" Au contacts |
| HARDWARE | |
| STYLE OF HARDWARE: | |
| 00 | None |
| JJ | Four #0-80 UNF* turning jackscrews, captivated, two on each connector |
| JT | Two #0-80 UNF* turning jackscrews, captivated, on plug & two #0-80 UNF* threaded holes** on receptacle |
| JP | Two #0-80 UNF* turning jackscrews, captivated, on plug & two #0-80 UNF* threaded holes** on plug |
| TJ | Two #0-80 UNF* threaded holes** on plug & two #0-80 UNF* turning jackscrews, captivated, on receptacle |
| JR | Two #0-80 UNF* turning jackscrews, captivated, on receptacle & two #0-80 UNF* threaded holes** on receptacle |
| TT | Four #0-80 UNF* threaded holes**, two on each connector |
| POLARIZATION / WIRING: | |
| XX | For wiring codes, see page NA-2 |

* = #2-56 UNC thread on 85, 91 position connectors
 .050 hex key (#0-80 thread)
 1/16" hex key (#2-56 thread)

Recommended torque value 1.0 inch-lbs. max. (#0-80 thread)
 Recommended torque value 2.0 inch-lbs. max. (#2-56 thread)
 Ball end hex wrench not recommended
 Hex wrench key/bit conforming to the requirements of ASME / ANSI-B-18.3 is recommended.
 .050" hex L-key long arm wrench - order AirBorn p/n CDG14148.
 1/16" hex L-key long arm wrench - order AirBorn p/n CDG14160.

** = Threaded hole tapped directly into stainless steel and titanium shells, aluminum shells have stainless steel inserts (as shown on previous page).

● Consult factory if jumpers require other than direct one to one connections.

= Option not RoHS compliant