

LEAD CONFIGURATION OPTIONS

NM-1J2-009-PS1-JTAW
XX-XXX-XXX-XXX-XXXX

SERIES									
NM .025" Metal I/O Connector									
BODY									
1	1-Row								
BODY STYLE:									
J	Jumper assembly								
BODY MATERIAL:									
2	Liquid Crystal Polymer with electroless nickel shell								
3	Liquid Crystal Polymer with electrodeposited cadmium shell ☒								
4	Liquid Crystal Polymer with stainless steel shell								
5	Liquid Crystal Polymer with titanium shell								
SIZE									
XXX Number of contacts (009, 015, 021, 025, 031, 037 or 051)									
CONTACTS									
TYPE CONTACTS/TERMINATIONS:									
PP	Plug to plug								
PS	Plug to receptacle								
SS	Receptacle to receptacle								
PLATING OPTIONS:									
1	50 µ" Au contacts								
HARDWARE									
STYLE OF HARDWARE:									
00	None								
JJ	Four #0-80 UNF* turning jackscrews, captivated, two on each connector								
JT	Two #0-80 UNF* turning jackscrews, captivated, on plug & two #0-80 UNF threaded holes** on receptacle								
JP	Two #0-80 UNF* turning jackscrews, captivated, on plug & two #0-80 UNF threaded holes** on plug								
TJ	Two #0-80 UNF threaded holes** on plug & two #0-80 UNF* turning jackscrews, captivated, on receptacle								
JR	Two #0-80 UNF* turning jackscrews, captivated, on receptacle & two #0-80 UNF threaded holes** on receptacle								
TT	Four #0-80 UNF threaded holes**, two on each connector								
POLARIZATION / WIRING:									
XX	For wiring codes, see page N-151								

* = Recommended torque value 1.0 inch-lbs. max.

Ball end hex wrench not recommended

Hex wrench key/bit conforming to the requirements of ASME / ANSI-B-18.3 is recommended.

.050" hex L-key long arm wrench - order AirBorn p/n CDG14148.

** = Threaded hole tapped directly into stainless steel and titanium shells, aluminum shells have stainless steel inserts (as shown on previous page).

● Consult factory if jumpers require other than direct one to one connections.

☒ = Option not RoHS compliant