


6		5			
ITEM	PART#	DESCRIPTION	QTY	UOM	
A	512160200	2.0 WtB Rec Hsg 2Ckt	1	PC	
B	593708000	2.0 WtB Crimp Rec Chn	2	PC	
C	----	WHITE PART ID LABEL	1	PC	

2		1	
FROM	TO	DESCRIPTION	COLOUR
A1	--	1X22AWG DISC SR-PVC BK UL10002	BLACK
A2	--	1X22AWG DISC SR-PVC BK UL10002	BLACK

PART NUMBER	TITLE	L1	L2(REF)
2244831020	MicroTPA 2.0 R-S 2ckt 50mm disc Sn	50±5	15
2244831021	MicroTPA 2.0 R-S 2ckt 100mm disc Sn	100±5	15
2244831022	MicroTPA 2.0 R-S 2ckt 150mm disc Sn	150±5	15
2244831023	MicroTPA 2.0 R-S 2ckt 300mm disc Sn	300±5	15
2244831024	MicroTPA 2.0 R-S 2ckt 600mm disc Sn	600±5	15



MOLEX P/N
MOLEX
BATCH WK/YR

DETAIL A

- NOTES:
1. CABLE ASSEMBLY MUST PASS 100% CONTINUITY AND POLARITY TEST.
 2. CONNECTOR VIEW SHOWN FROM MATING SIDE.
 - 3.LABEL TEXT MUST BE 2 MM MAX. IN HEIGHT WITH ARIAL FONT.
 - 4.LABEL MUST BE WRAPPED IN FLAG TYPE ON A SINGLE CABLE.
 - 5.TINNING SHOULD BE DONE WITH LEAD FREE SOLDER BAR ONLY.
 - 6.FREE ENDS MUST BE STRIPPED,TWISTED &TINNED.THE LENGTH OF TINNING IS 5±1MM.TINNING DIA MUST BE 0.90 MM MAX.

REVISION			
DATE	REV	DESCRIPTION	CHANGER
2023/01/04	A	INITIAL RELEASE	THANUB
RELEASE STATUS	P1	RELEASE DATE	2023/02/08 09:35:32

FUNCTIONAL SYMBOLS $\frac{F}{A} = 0$ $\frac{F}{E} = 0$ $\frac{F}{P} = 0$ DIVISIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
	DIMENSION UNITS	SCALE
	mm	NTS
	GENERAL TOLERANCES (UNLESS SPECIFIED)	
	ANGULAR TOL	± °
	4 PLACES	±
	3 PLACES	±
	2 PLACES	±
	1 PLACE	±
	0 PLACES	±
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	
	THIRD ANGLE PROJECTION	DRAWING
		A4-SIZE
	SERIES	MATERIAL NUMBER
	224483	SEE TABLE
	CUSTOMER	SHEET NUMBER
	GENERAL MARKET	1 OF 1

EC NO: 736615
DRWN: THANUB 2023/01/04
CHK'D: SKUMAR07 2023/02/08
APPR: SKUMAR07 2023/02/08

INITIAL REVISION:
DRWN: THANUB 2023/01/04
APPR: SKUMAR07 2023/02/08

molex

SEE TABLE

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
2244831020	PSD	000	A